NOTES:


1. WAVELENGTH RANGE: 400 - 700nm:


2. COATING: UNCOATED


3. FINE GRIND SURFACE

4. ROHS COMPLIANT









SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2
SHAPE	PLANO	PLANO
SURFACE ACCURACY	COMMERCIAL POLISH	COMMERCIAL POLISH
SURFACE QUALITY	80-50	80-50
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION	$\phi \Box$	
ALL DIMS IN	mm	I

	Edr	nun	d	Opt	ics®
	25mm DI	IA. WHITE	DIFF	USING GL	.ASS

1	TITLE	25mm DIA. WHITE DIFFUSING GLAS	5
	DWG NO	34473	SHEET 1 OF 1