






NOTES:

- 1. SUBSTRATE:
BOROFLOAT®
- 2. COATING SPECIFICATION:
S1: Enhanced Aluminum (450-650nm)
R(AVG) >95% @ 450 - 650nm
- 3. FINE GROUND SURFACE
- 4. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

| | | | | | | |
|-----------------|--|----------------------|----------------------|--|-------|---|
| | | S1 | S2 |  Edmund Optics® | | |
| SHAPE | | PLANO | PLANO | THIRD ANGLE PROJECTION  | TITLE | 21 x 30mm Enhanced Aluminum, λ/4 Mirror |
| SURFACE QUALITY | | 60-40 | GROUND | | | |
| CLEAR APERTURE | | 17.85 x 25.50 | N/A | | | |
| BEVEL | | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED | ALL DIMS IN | mm | DWG NO 43507 |
| | | | | | | SHEET 1 OF 1 |