## NOTES:

1. SUBSTRATE MATERIAL: FLOAT GLASS


2. ROHS COMPLIANT


3. COATING (APPLY ACROSS CLEAR APERTURE)

S1: 50% R ±5% @ 550nm 50% T ±5% @ 550nm

S2: NONE

**EDGES CUT** 





## FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	\$1	\$2
SHAPE	PLANO	PLANO
SURFACE QUALITY	80-50	80-50
SURFACE FLATNESS	4 - 6λ	4 - 6λ
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

			<b>Edmund Optics</b> ®	
THIRD ANGLE PROJECTION	$\phi$	TITLE	18 x 30mm, 50 R/50 T, PLATE BEAMSPLI	TTER
ALL DIMS IN	mm	DWG NO	31414	SHEET

SHEET 1 OF 1 31414