NOTES:

1. SUBSTRATE MATERIAL: FLOAT GLASS


2. ROHS COMPLIANT


3. COATING (APPLY ACROSS CLEAR APERTURE)

S1: 70% R ±5% @ 550nm 30% T ±5% @ 550nm

S2: AR 1/4λ MgF2 @ 550nm







PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	\$1	\$2		
SHAPE	PLANO	PLANO		
SURFACE QUALITY	80-50	80-50		
SURFACE FLATNESS	4 - 6λ	4 - 6λ		
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED		

	THIRD ANGLE PROJECTION	$\phi \Box$	TIT
_	ALL DIMS IN	mm	D۱

	Edmund Optics®	
TITLE 12.5 x 17.5	mm, 70 R/30 T, PLATE BEAMSPLITTER	

1 OF 1

	Υ `			
ALL DIMS IN	mm	DWG NO	45317	SHEET 1 OF 1