

NOTES:


- 1. SUBSTRATE: N-BK7
- 2. S2 TO BE PARALLEL WITH S1 TO < 1 ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE) \$1 & \$2: R(AVG) ≤0.4% @ 425 - 675nm



5. RoHS COMPLIANT







FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

| | \$1 | \$2 |
|-----------------|----------------------|----------------------|
| SHAPE | PLANO | PLANO |
| SURFACE QUALITY | 60-40 | 60-40 |
| CLEAR APERTURE | Ø22.50 | Ø22.50 |
| BEVEL | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED |

| | THIRD ANGLE_ PROJECTION | | TI |
|---|----------------------------|----|----|
| _ | ALL DIMS IN | mm | D' |

| e | Edmund Optics® |
|-------|--|
| TITLE | 25mm DIA., 3mm THICK, VIS 0° COATED $\lambda/4$ N-BK7 WINDOW |

| MS IN | mm | DWG NO | 37005 | SHEET 1 OF 1 |
|-------|----|--------|-------|-----------------|
| | | | | |