
NOTES:


- 1. SUBSTRATE: N-BK7
- 2. S2 TO BE PARALLEL WITH S1 TO < 1 ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE) \$1 & \$2: R(AVG) ≤1.75% @ 400 - 700nm



5. Rohs Compliant







FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2	
SHAPE	PLANO	PLANO 60-40	
SURFACE QUALITY	60-40		
CLEAR APERTURE	Ø45.00	Ø45.00	
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	

		8	[®] Edmund Optics [®]	
THIRD ANGLE PROJECTION		TITLE	50mm DIA., 2mm THICK, MgF2 COATED λ/4 N- BK7 WINDOW	
ALL DIMS IN	mm	DWG NO	37011	SHEET 1 OF 1