



NOTES:


1. COATING (APPLY ACROSS COATING APERTURE)  
 T(AVG): >80% FROM 400 - 575  
 CUT-OFF WAVELENGTH: 600nm ± 3%  
 BLOCKING RANGE: 625 - 735nm
2. RoHS: COMPLIANT



**FOR INFORMATION ONLY:  
 DO NOT MANUFACTURE  
 PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
 DIMENSIONS ARE FOR REFERENCE ONLY



	S1	S2	THIRD ANGLE PROJECTION 		TITLE	600nm, 12.5mm Square, OD 2 Ultra-Thin Shortpass Filter	
SHAPE	PLANO	PLANO	ALL DIMS IN	mm	DWG NO	35894	SHEET 1 OF 1
CLEAR APERTURE	11.25 x 11.25	11.25 x 11.25					
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED					