NOTES:


1. SUBSTRATE: FUSED SILICA


2. RoHS: COMPLIANT

3. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN < 5 ARCMIN

4. COATING (APPLY ACROSS COATING APERTURE) \$1& \$2: 1/4 WAVE MgF2 @ 550nm R(AVG) < 1.75% FROM 400 - 700nm







FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

SHAPE	S1 PLANO	S2 PLANO			Edmund Optic	CS®
SURFACE ACCURACY SURFACE QUALITY	1λ 60-40	1λ 60-40	THIRD ANGLE PROJECTION	TITLE	50mm DIA. MgF2 COATED, 1λ FUSED SILI WINDOW	ICA
CLEAR APERTURE	Ø45.00	Ø45.00	'		77112571	CHEET
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN mm	DWG NO	11927	SHEET 1 OF 1

