




NOTES:

- 1. COATING:
S1: METAL VELVET™
THICKNESS (µm) 5-7
- 2. ABSORBANCE: 99.9% (0-10°)%
- 3. ABRASION RESISTANCE: LIGHT, DO NOT TOUCH
- 4. HUMIDITY RESISTANCE: MIL-C-48497A
- 5. OPERATING TEMPERATURE (°C): -40 to 150
- 6. WAVELENGTH RANGE: 0.3 - 14
- 7. TYPICAL ADHESIVE OUTGASSING PERFORMANCE:
0.85% TML
0% VCM
PER ASTM E595-77/84/90



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

 Edmund Optics®			
THIRD ANGLE PROJECTION 		TITLE	Metal Velvet Low Outgassing Adhesive Foil Sheet 200 x 300mm
ALL DIMS IN	mm	DWG NO	12515
			SHEET 1 OF 1