



NOTES:

- 1. SUBSTRATE:
N-BK7
- 2. COATING (APPLY ACROSS COATING APERTURE)
NONE
- 3. SURFACE QUALITY: 60-40
- 4. WAVELENGTH RANGE: 350 - 2200 nm



SECTION A-A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

Edmund Optics®

THIRD ANGLE PROJECTION		TITLE	100mm Diameter x 4mm Thickness, N-BK7 Glass Dome	
ALL DIMS IN	mm	DWG NO	64499	SHEET 1 OF 1