NOTES:

1. SUBSTRATE MATERIAL: Float Glass

2. COATING (APPLY ACROSS CLEAR APERTURE, SPECIFICATION APPLIES AFTER SANDBLASTING):


S1: R(AVG) >95% @ 450 - 650nm


S2: NONE



FINE GRIND SURFACE

ROHS: COMPLIANT





SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

PARTS TO THIS DRAWING

S2	THIRD ANG PROJECTIO	
N/A		
	ALL DIMS I	

Edmund Optics	S [®]
---------------	----------------

	THIRD ANGLE PROJECTION	$\phi \Box$	TITLE	50mm Dia. Enhanced Aluminum Coa Reflective Diffuser	ted,
ED	ALL DIMS IN	mm	DWG NO	12455	SHEET 1 OF 1

	\$1	\$2	TI P	
MIN CLEAR APERTURE	Ø47.50	N/A	_	
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	,	