## NOTES:


MATERIAL:


HOUSING: STAINLESS STEEL LENS: D-ZLaF52LA


2. COATING (APPLY ACROSS CLEAR APERTURE) R(AVG) <0.4% @ 1050 - 1600nm

3. CLEAR APERTURE: 5.00 mm

4. RoHS: COMPLIANT







SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

## FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

THIRD ANGLE PROJECTION		TITLE	1550nm Alignment, 0.40 NA Fiber Collir w/ SMA Connector	550nm Alignment, 0.40 NA Fiber Collimator w/ SMA Connector	
ALL DIMS IN	mm	DWG NO	83731	SHEET 1 OF 1	