



- NOTES:
1. MIRROR SUBSTRATE: FUSED SILICA
  2. COATING (APPLY ACROSS CLEAR APERTURE)  
1000Å THICK LOW PINHOLE, PROTECTED SILVER
  3. RoHS: COMPLIANT



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

**EO<sup>®</sup> Edmund Optics<sup>®</sup>**

	VALUE	THIRD ANGLE PROJECTION 		TITLE	6210H 5mm MIRROR SINGLE AXIS GALVANOMETER SCANNER, PROTECTED SILVER	
MIN CLEAR APERTURE	Ø5mm	ALL DIMS IN	mm	DWG NO	11762	SHEET 1 OF 1