



PART	PART #	MATERIAL
①	#32-757	SCHOTT RG780
②	#56-353	BLACK ANODIZED ALUMINUM




SECTION A-A

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

SHAPE	PLANO
SPECTRAL TRANSMITTANCE (%)	97
PASSBAND LIMIT 1 (nm)	900
CUT-OFF POSITION (nm)	780±9
STOPBAND LIMIT (nm)	610
WAVELENGTH	IR

THIRD ANGLE PROJECTION 		 Edmund Optics®	
ALL DIMS IN mm		TITLE	22mm CA, SCHOTT RG780, C-Mount Longpass Glass Color Filter
DWG NO		13037	SHEET 1 OF 1