



NOTES:
1. RoHS: COMPLIANT

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



	VALUE
DESIGN WAVELENGTH DWL (nm)	355
INPUT DIAMETER (mm)	12.0 - 12.1mm (1/e ²)
WAVELENGTH RANGE (nm)	330 - 380



ALL DIMS IN mm

TITLE

355nm Flat Top Beam Shaper | πShaper
12_12_355_HP

DWG NO

15497

SHEET
1 OF 1