




NOTES:

1. CONSTRUCTION: BLACK ANODIZED ALUMINUM
2. TECHNOLOGY: Hexa-Black™
3. ABSORBANCE (%): 99.9
4. WAVELENGTH RANGE (nm): 200 - 5,000

HEXA-BLACK STRUCTURE FOR REFERENCE



INSIDE OF EXTENSION TUBE IS COVERED IN HEXA-BLACK



SECTION A-A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



| | | | | |
|------------------------|----|--------|--|--------------|
| THIRD ANGLE PROJECTION | | TITLE | 15mm Length, Acktar Hexa-Black™ C-Mount Noise Reduction Extension Tube | |
| ALL DIMS IN | mm | DWG NO | 15481 | SHEET 1 OF 1 |