
## NOTES:


- 1. SUBSTRATE: N-BK7
- 2. S2 TO BE PARALLEL WITH S1 TO < 1ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE) \$1 & \$2: R(AVG) ≤0.5% @ 600 - 1050nm



5. Rohs Compliant







## FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2			
SHAPE	PLANO	PLANO			
SURFACE QUALITY	60-40	60-40			
CLEAR APERTURE (mm)	Ø45.72	Ø45.72			
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED			

			<b>Edmund Optics</b> ®		
THIRD ANGLE PROJECTION		TITLE	50.8mm DIA., 4mm THICK, NIR I COATE N-BK7 WINDOW	D λ/4	
)	ALL DIMS IN	mm	DWG NO	15442	SHEET 1 OF 1