



NOTES:

1. SUBSTRATE: ISUZU ISK150  
 DENSITY: 2.58g/cm<sup>3</sup>  
 REFLECTION FACTOR: 0.92  
 KNOOP HARDNESS: 497kg/mm<sup>2</sup>  
 REFRACTIVE INDEX: 1.516nm
2. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN 3 ARCMIN


**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1
SHAPE	PLANO
FUNCTION	HEAT ABSORBING
SURFACE QUALITY	60-40
CLEAR APERTURE	$\varnothing 11.25$
BEVEL MAX FACE	PROTECTIVE AS NEEDED

THIRD ANGLE  
PROJECTION



ALL DIMS IN

mm



**Edmund Optics®**

TITLE

ISUZU ISK150, 12.5 Dia., HEAT ABSORBING  
COLORED GLASS FILTER

DWG NO

15699

SHEET  
1 OF 1