



NOTES:

- 1. SUBSTRATE:
POLYMER FILM XP42-18 WITH ADHESIVE
- 2. TEMPERTURE RESISTANCE (°C x HOURS):
HEAT: 80 x 500
COLD: -40 x 500
HUMIDITY: 60 x 90% RH x 500
- 3. WAVELENGTH RANGE: 400 - 700 nm
- 4. POLARIZATION EFFICIENCY (%): >99.98
- 5. TRANSMISSION (%):
SINGLE: 42
PARALLEL: 36
CROSSED: <0.004 @ 546nm
- 6. EXTINCTION RATIO: 9000:1
- 7. ROHS COMPLIANT



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

 Edmund Optics®			
THIRD ANGLE PROJECTION 		TITLE	600 x 1000mm LINEAR POLARIZING FILM (XP42-18) WITH ADHESIVE
ALL DIMS IN	mm	DWG NO	16019
			SHEET 1 OF 1