




NOTES:

- 1. SUBSTRATE MATERIAL:
FLOAT GLASS
- 2. COATING (APFLOW ACROSS CLEAR APERTURE):
S1: ALUMINUM
S2: NONE
- 3. WAVELENGTH RANGE: 190 - 900nm
NOMINAL BLAZE WAVELENGTH: 250nm
GROOVE DENSITY:1800 GROOVES/mm

4. EDGES GROUND


- 5. RoHS COMPLIANT



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

EO[®] Edmund Optics[®]

			THIRD ANGLE PROJECTION 		TITLE	1800 GROOVES, 30x30mm, 190-900nm HOLOGRAPHIC HIGH PERFORMANCE REFLECTION GRATING	
SHAPE	S1 PLANO	S2 PLANO	ALL DIMS IN	mm	DWG NO	15750	SHEET 1 OF 1
CLEAR APERTURE	27.0 x 27.0	27.0 x 27.0					