



NOTES:

- 1. SUBSTRATE MATERIAL: N-BK7
- 2. ROHS COMPLIANT
- 3. COATING (APPLY ACROSS CLEAR APERTURE)
 - S1: R(AVG) > 98% @ 340 - 488nm @ 0°, ALL POLARIZATIONS
 - R(AVG) > 98% @ 320 - 450nm @ 45°, ALL POLARIZATIONS
 - R(AVG) > 99% @ 320 - 450nm @ 45°, S-POLARIZATION

S2: NONE


4. FINE GRIND SURFACE



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**


SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
ANGLE TOL. (arcmin)	±2	±2
SURFACE QUALITY	40-20	40-20
SURFACE FLATNESS	λ/8	λ/8
CLEAR APERTURE	90%	90%
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED



TITLE	20.0mm 320 - 450nm COATED, N-BK7 RIGHT ANGLE MIRROR		
DWG NO	15597	SHEET 1 OF 1	

THIRD ANGLE PROJECTION



ALL DIMS IN	mm
-------------	----