



NOTES:

1. SUBSTRATE MATERIAL:
SCHOTT: N-BK7
2. BEAM DEVIATION: <3 arcmin
3. COATING (APPLY ACROSS CLEAR APERTURE)
S1, S2, S3, & S4: 1/4 WAVE MGF2 @ 900nm
R(AVG) <1.75% FROM 700 - 1100nm
S5: MULTILAYER DIELECTRIC
T(ABS) = 50% ± 5% @ 900nm
T(AVG) = 50% ± 10% FROM 700 TO 1100nm

4. FINE GROUND SURFACE
5. ELEMENTS TO BE CEMENTED WITH NORLAND OPTICAL ADHESIVE NOA 61
6. PROTECTIVE BEVEL AS NEEDED
7. MARK IDENTIFIES BEAMSPLITTER COATED RIGHT ANGLE PRISM



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1, S2, S3, S4	S5	EFL (AT 587.6nm)	NA	 Edmund Optics®		
SHAPE	PLANO	PLANO	BFL (AT 587.6nm)	NA	TITLE	25mm 50R/50T Standard NIR Cube Beamsplitter	
IRREGULARITY AT 632.8nm (P-V)	1/4 WAVE	1/4 WAVE	ALL DIMS IN	mm	DWG NO	14643	SHEET 1 OF 1
SURFACE QUALITY	40-20	40-20					
MIN CLEAR APERTURE	22.50 x 22.50	31.82 x 22.50					