


TECHSPEC® Ultrafast Broadband Mirrors


500 - 540nm Reflectance
FOR REFERENCE ONLY



© COPYRIGHT 2020 EDMUND OPTICS, INC. ALL RIGHTS RESERVED

TECHSPEC® Ultrafast Broadband Mirrors


500 - 540nm GDD Performance
FOR REFERENCE ONLY



© COPYRIGHT 2020 EDMUND OPTICS, INC. ALL RIGHTS RESERVED

TECHSPEC® Ultrafast Broadband Mirrors


1000 - 1070nm Reflectance
FOR REFERENCE ONLY



© COPYRIGHT 2020 EDMUND OPTICS, INC. ALL RIGHTS RESERVED

TECHSPEC® Ultrafast Broadband Mirrors

1000 - 1070nm GDD Performance
FOR REFERENCE ONLY



© COPYRIGHT 2020 EDMUND OPTICS, INC. ALL RIGHTS RESERVED