




NOTES:

- 1. SUBSTRATE:
POLYMER FILM
- 2. POLARIZATION: > 88% EFFICIENCY
- 3. TRANSMISSION:
SINGLE: 38
PARALLEL: 32
CROSSED: 0.76
- 4. UV ABSORPTION: >88%
- 5. OPERATING TEMPERATURE: -50 TO 70°C
- 6. WAVELENGTH RANGE: 450 - 675 nm
- 7. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

THIRD ANGLE PROJECTION 		 Edmund Optics®	
TITLE		8.5" x 15" Linear Polarizing Film	
ALL DIMS IN	mm	DWG NO	SHEET 1 OF 1
		19292	