




NOTES:

1. SUBSTRATE: Fused Silica (Corning 7980)
  2. ROHS: COMPLIANT
  3. SURFACE S2 TO BE PARALLEL TO SURFACE S1 WITHIN <5 ARCMIN
  4. COATING(APPLY ACROSS CLEAR APERTURE)
- S1 & S2: NONE
5. TRANSMITTED WAVEFRONT DISTORTION:  $\leq 1\lambda$

6. FINE GRIND SURFACE



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	60-40	60-40
CLEAR APERTURE	$\phi 22.50$	$\phi 22.50$
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

THIRD ANGLE PROJECTION

ALL DIMS IN mm

**EO**® Edmund Optics®

TITLE

25mm Dia. 3mm Thick Uncoated, 1λ Fused Silica Window

DWG NO

19838

SHEET 1 OF 1