




NOTES:


1. SUBSTRATE: POLYMER FILM XP42-100
2. OPERATING TEMPERATURE (°C): -10 to +60
3. OPERATING HUMIDITY (%): ≤80 (No Condensation)
4. WAVELENGTH RANGE: 400-700nm
5. POLARIZATION: >99.98
6. TRANSMISSION (%):
SINGLE 42 ±2
PARALLEL: 36.4
CROSSED: <0.004
7. ROHS COMPLIANT



FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® **Edmund Optics®**

THIRD ANGLE PROJECTION 		TITLE	100 x 100mm Linear Polarizer (XP42-100)	
ALL DIMS IN	mm	DWG NO	19955	SHEET 1 OF 1