NOTES:


1. SUBSTRATE:

AS87ECO

2. COATING (APPLY ACROSS CLEAR APERTURE)

S1 & S2: NONE

3. ROHS COMPLIANT





SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

| SHAPE | \$1 PLANO | S2 PLANO | | | | Edmund Optic | S® |
|-------------------|---------------------|---------------------|------------------------|-----|--------|---------------------------------------|-----------------|
| SURFACE QUALITY | 80-50 | 80-50 | | 1 . | | SCHOTT AS87ECO, 50.8 x 76.2mm, 0.1n | mm |
| SURFACE ROUGHNESS | < 0.50nm | < 0.50nm | THIRD ANGLE PROJECTION | | TITLE | Thick, Ultra-Thin Window | |
| CLEAR APERTURE | 45.72 x 68.58 | 45.72 x 68.58 | | ' | | · · · · · · · · · · · · · · · · · · · | |
| BEVEL | PROTECTED AS NEEDED | PROTECTED AS NEEDED | ALL DIMS IN | mm | DWG NO | 20204 | SHEET 1 OF 1 |