

NOTES:

- 1. SUBSTRATE: FUSED SILICA
- 2. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN < 5 ARCSEC
- COATING (APPLY ACROSS COATING APERTURE):
 \$1 & \$2: R(ABS) ≤ 1.0% FROM 250-425nm @ 0° AOI R(AVG) ≤ 0.75% FROM 250-425nm @ 0° AOI R(AVG) ≤ 0.5% FROM 370-420nm @ 0° AOI



5. ROHS COMPLIANT





FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

SHAPE	\$1 PLANO	\$2 PLANO			Edmund Optics®	3
SURFACE QUALITY	20-10	20-10	Ţ		50.8mm Dia., 5mm Thick, UV-AR λ/10 Fusec	7
TRANSMITTED WAVEFRONT (P-V)	λ/10	λ/10	THIRD ANGLE PROJECTION	TITLE	Silica Window	۱
CLEAR APERTURE	Ø45.72	Ø45.72				
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN mm	DWG NO		SHEET 1 OF 1