




- NOTES:
- 1. SUBSTRATE:
H-K9L
 - 2. COATING (APPLY ACROSS CLEAR APERTURE)
S1: NONE
S2: NONE
 - 3. CENTERING: ≤ 30 ARCMIN



FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL @ 587.6nm	15.50	 Edmund Optics®		
SHAPE	CONVEX	PLANO	BFL @ 587.6nm	10.87			
SURFACE QUALITY	80-50 (typical)	80-50 (typical)			TITLE	18mm Dia. x 15.5mm FL, Aspheric Condenser Lens	
CLEAR APERTURE	Ø 16.20	Ø 16.20					
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED	ALL DIMS IN	mm	DWG NO	22843	SHEET 1 OF 1