





- NOTES:
- 1. SUBSTRATE:
LIBA2000+
 - 2. COATING (APPLY ACROSS CLEAR APERTURE)

S1: NONE
S2: NONE
 - 3. CENTERING: ≤25 ARCMIN



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

PARTS TO THIS DRAWING			EFL @ 587.6nm	28.50	 Edmund Optics®				
	S1	S2	BFL @ 587.6nm	16.90					
SHAPE	CONVEX	PLANO			TITLE	40mm Dia. x 28.5mm FL, Uncoated, Molded Condenser Lens with Medium Diffuser			
SURFACE QUALITY	AS MOLDED	MEDIUM DIFFUSER							
CLEAR APERTURE	Ø 32.40	Ø 32.40			DWG NO	22684			
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED							
			ALL DIMS IN	mm					
						SHEET	1 OF 1		