


NOTES:

1. COATING (APPLY ACROSS COATING APERTURE)

DURABILITY: MIL-C-48497A
PERFORMANCE SPECIFICATIONS:
CWL: 532
FWHM: 12 NOMINAL
TRANSMISSION %: 85% (400-500nm); 90% (600-1500nm)

2. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS
APPLY ACROSS CLEAR APERTURE

3. ROHS COMPLIANT



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

EO® Edmund Optics®

S1		S2		<div>THIRD ANGLE PROJECTION</div>		TITLE		532nm 70 x 375mm META® holoOPTIX® FLEX Notch Filter	
SHAPE	PLANO		PLANO	ALL DIMS IN	mm	DWG NO	23031	SHEET 2 OF 3	