





- NOTES:
- 1. SUBSTRATE: SODIUM SILICATE GLASS DOPED WITH SILVER NANOPARTICLES
 - 2. COATING: Uncoated
 - 3. TYPICAL ENERGY DENSITY LIMIT: 10 W/cm²
 - 4. EXTINCTION RATIO: >10,000:1
 - 5. WAVELENGTH RANGE: 1500-1600
 - 6. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	 Edmund Optics®			
SHAPE	PLANO	PLANO				
SURFACE QUALITY	40 - 20	40 - 20		TITLE	Ultra-Thin Polarizer, 1550nm, 10 x 10mm, Unc.	
TRANSMISSION (%)	>88	>88		DWG NO	26650	SHEET 5 OF 6
ACCEPTANCE ANGLE	±20°	±20°				
BEVEL MAX FACE	PROTECTED AS NEEDED	PROTECTED AS NEEDED	ALL DIMS IN	mm		