




- NOTES:
- 1. SUBSTRATE: CTA (CELLULOSE TRIACATE)
 - 2. OPERATING TEMPERTURE: -20 to +70
 - 3. WAVELENGTH RANGE: 400 - 700
 - 4. EXTINCTION RATIO: 15,000:1 (NOMINAL)
 - 5. TRANSMISSION, T_p (%): >42
 - 6. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

THIRD ANGLE PROJECTION 		 Edmund Optics®	
TITLE		1000mm x 620mm, Ultra High Contrast Linear Polarizing Film	
ALL DIMS IN	mm	DWG NO	SHEET 1 OF 6
		26916	