





- NOTES:
- COATING:
S1: SPECTRAL BLACK™
THICKNESS: 3 - 7 (µm)
 - ABSORBANCE: 99.5 - 99.7 (0 - 10° AOI) %
 - ABRASION RESISTANCE: MODERATE
 - HUMIDITY RESISTANCE: MIL-C-48497A
 - OPERATING TEMPERATURE (°C): -196 TO +350
 - WAVELENGTH RANGE (µm): 0.3 - 14



DETAIL A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

<div> <div>EO[®]</div> <div>Edmund Optics[®]</div> </div>			
<div>THIRD ANGLE PROJECTION</div> 		<div>TITLE</div> <div>10 x 10cm Sheet of Spectral Black Foil, No Adhesive</div>	
<div>ALL DIMS IN</div> <div>mm</div>	<div>DWG NO</div> <div>28940</div>	<div>SHEET</div> <div>1 OF 1</div>	