



NOTES:

- 1. COATING:
S1: SPECTRAL BLACK™
THICKNESS: 3 - 7 (µm)
- 2. ABSORBANCE: 99.5 - 99.7 (0 - 10° AOI) %
- 3. ABRASION RESISTANCE: MODERATE
- 4. HUMIDITY RESISTANCE: MIL-C-48497A
- 5. OPERATING TEMPERATURE (°C): -40 to 121
- 6. WAVELENGTH RANGE(µm): 0.3 - 14




DETAIL A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



| | | | | |
|--|----|--------|--|-----------------|
| THIRD ANGLE PROJECTION  | | TITLE | 10 x 10cm Sheet of Spectral Black Foil, Standard Adhesive | |
| ALL DIMS IN | mm | DWG NO | 28941 | SHEET 1 OF 1 |