





NOTES:

- 1. SUBSTRATE:  
TAC FILM
- 2. COATING (APPLY ACROSS CLEAR APERTURE)  
S1 & S2: NONE
- 3. PROTECTIVE FILM ON NON-MATTE SURFACE SHOULD BE REMOVED BEFORE USE
- 4. WAVELENGTH RANGE: 300 - 1100NM
- 5. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

THIRD ANGLE PROJECTION 		 Edmund Optics®	
TITLE		12.5 x 12.5mm Light Diffusing Film	
ALL DIMS IN	mm	DWG NO	SHEET
		27102	1 OF 6