



- NOTES:
- 1. SUBSTRATE:  
PMMA, PERMANENTLY LAMINATED TO PET FILM WITH HARD MICROSTRUCTURED POLYMER COATING
  - 2. TYPE OF DIFFUSER: Angle Bending Diffuser
  - 3. DIFFUSING ANGLE (°): 60 x 20, with 8° Angle Bend
  - 4. OPERATING TEMPERATURE (°C): -34 to +70



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

**EO<sup>®</sup> Edmund Optics<sup>®</sup>**

THIRD ANGLE PROJECTION 		TITLE	50mm Dia., 8° Bend Angle, Angle Bending Diffuser	
ALL DIMS IN	mm	DWG NO	70769	SHEET 3 OF 11