DATA SHEET


S4LFT1420-328

F-THETA STANDARD - FUSED SILICA 1030 - 1090 nm



ILLUSTRATION ONLY

OUTLINE DRAWING



All information contained in this data sheet is for information purposes only and is not binding. The content is subject to change at any time without notification, all information without guarantee. We reserve the right to make constructional changes in the course of product improvement. Copyright © Sill Optics GmbH • All rights reserved




DATA SHEET

SPECIFICATIONS


	0.41 FT4 400 000
article number	S4LFT1420-328
design wavelength [nm]	1064
effective focal length [mm]	420.0
working distance [mm]	499.2
max. entrance beam-Ø [mm]	14.0
aperture stop distance [mm]	28.3
scan area for a 2 mirror system with mirror distance from lens housing for mirror 2 / mirror 1 [mm x mm]	280 x 280 19.8 / 36.8
max. telecentricity error [°]	17.3
total transmission [%]	> 97
absorption [ppm]	92
lens material	fused silica
LIDT (coating)	5.0 J/cm² per 1ns pulse at 50Hz
SP and USP usable	yes
weight [kg]	1.0
cover glass	S4LPG4160-328
cleanliness	not specified

SPOT



spot diameter at 86.5% level for a Gaussian beam (M² = 1) with 14.0 mm diameter at $1/e^2$, clipped at 14.0 mm field size and mirror distances as given above for a two mirror scan system

BACK REFLECTION POSITIONS



REMARKS

The stated values are based on a vignetting of less than 1 %.

Effective focal length and working distance have a tolerance of +/- 1.5 %.

Absorption tolerance +/- 25 %. Absorption may increase. Correct cleaning establishes original condition.

All information contained in this data sheet is for information purposes only and is not binding. The content is subject to change at any time without notification, all information without guarantee. We reserve the right to make constructional changes in the course of product improvement. Copyright © Sill Optics GmbH • All rights reserved

